










#### Handheld Flashlight and Work light One unit, Two roles

- Safety Holder that can be attached to the vertical harness belt
- 3 modes of brightness: 350 lm, 150 lm, and 15 lm
- To relieve eye strains, low to high mode: 15 lm, 150 lm and 350 lm
- Flicker-Free light
- The hole for attaching devices to prevent drop
- Powerful Neodymium Magnet on the back side

#### **Specifications**









ITEM CODE	CASE	MASTER CARTON	UPC
LE-SF351D	6	24	0-49296-26681-3





Display Size

W 17.7 in (450 mm) H 9.8 in (250 mm)





www.tajimatool.com

@tajimatoolusa

For more information, please contact our marketing department at orderdesk@tajimatool.com

TAJIMA TOOL CORPORATION 3510 Torrance Blvd., Suite 301, Torrance, CA 90503

Toll-Free Phone: 1-888-482-5462 www.tajimatool.com

© 2021 TAJIMA TOOL CORPORATION. ALL RIGHTS RESERVED.

No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, without the prior written permission of the publisher.



TaJima

HOT NEWS

# **NEW** GRATI-LITE LE-F501D

## LE-F501D





#### **Battery Operated Headlamp**

- Illuminated surface diameter is approximately 39.3 in ( 100 cm ) when emitted at 19.6 in ( 50 cm ) away from the subject
- The external battery compartment can be easily opened or closed while wearing gloves



#### Specifications

Specifications				
FL1 STANDARD MODE 3 MODE 2 MODE 1				
31/2	500 LUMENS	250 LUMENS	50 LUMENS	
(1)	6h	10h	25h	
	118m			





ITEM CODE	CASE	MASTER CARTON	UPC
LE-F501D	6	24	0-49296-26679-0

## TaJima LED Headlamp

### LE-F501D & LE-M501D



It's Wide-Angle beam



Angle Adjustment Function



Switching 3 modes: 50 lm, 250 lm and 500 lm, by pushing the button



Helmet clip to prevent headband slippage



Minimal flicker and glare to relieve eye strain



When the battery runs low, the light itself flashes as a warning



# LE-M501D



## Self-Contained Battery Operated Headlamp

- Illuminated surface diameter is approximately 39.3 in ( 100 cm ) when emitted at 19.6 in ( 50 cm ) away from the subject
- Powerful Neodymium Magnet on the back side
- Detachable, rotate and slide mechanism
- Shut-off mode prevents accidental activation and battery depletion when stored for an extensive amount of time







Specifications

FL1 STANDARD	MODE 3	MODE 2	MODE 1
31/2	500 LUMENS	250 LUMENS	50 LUMENS
(1)	4h	6h	15h





ITEM CODE	CASE	MASTER CARTON	UPC
LE-M501D	6	24	0-49296-26680-6